

Lighting element for surface-mounted housing

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--------------------|-----------|--------------|------------------------|----|---------------|
| cream white glossy | 1067 01 | 1/5 | 22.69 | 02 | 4010337105169 |
| pure white glossy | 1067 03 | 1/5 | 22.69 | 02 | 4010337107088 |

Features

- The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.

Technical data

| | |
|----------------------|------------------|
| Rated voltage: | AC 230 V, 50 Hz |
| Power consumption: | 0.05 W / 1.65 mA |
| Light intensity: | 0.2 cd |
| Ambient temperature: | 0 °C to +40 °C |