

Light bulb dimming insert with pressure/2-way switch

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
100 – 1000 W	1181 00	1/5	183.69	02	4010337003939

Features

- Dimming light bulbs and HV halogen lamps at AC 230 V, 50 Hz.
- Electronic short-circuit protection.
- Automatic excess-temperature protection with restart.
- With screw terminals.

Technical data

Rated voltage:	AC 230/240 V, 50 Hz
Connected load at 25 °C	
- Light bulbs:	100 to 1000 W
- HV halogen lamps:	100 to 1000 W
Installation depth:	32 mm
Connection cross section	
- maximum:	2.5 mm ²
Ambient temperature:	+5 °C to +45 °C

Notes

- If the ambient temperature is higher than 25 °C, the connected load must be reduced.