

Continuous controller with button interface, 4-gang for KNX

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--------------------|-----------|--------------|------------------------|----|---------------|
| cream white glossy | 2100 01 | 1 | 317.84 | 06 | 4010337048022 |
| pure white glossy | 2100 03 | 1 | 317.84 | 06 | 4010337048039 |
| pure white matt | 2100 27 | 1 | 317.84 | 06 | 4010337048060 |
| anthracite | 2100 28 | 1 | 320.21 | 06 | 4010337048077 |
| colour aluminium | 2100 26 | 1 | 324.06 | 06 | 4010337048053 |
| black matt | 2100 005 | 1 | 324.06 | 06 | 4010337037255 |
| grey matt | 2100 015 | 1 | 324.06 | 06 | 4010337083016 |
| stainless steel | 2100 600 | 1 | 330.84 | 06 | 4010337021520 |

Features

- The setpoint value is changed using the adjustment dial.
- A presence button is used to switch between Comfort and Standby mode.
- The current statuses are displayed on the continuous controller by LEDs.

Technical data

Installation depth: 23 mm

Connection cross section

- J-Y(St)Y: $2 \times 2 \times 0.8 \text{ mm}^2$
