

**USB power supply insert, 2-gang
Type A / type A**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
black	2359 00	1/5	65.42	02	4010337084655

Features

- Charging option for up to two end devices simultaneously using USB cable type A.
- Suitable as a charging device, e.g. for mobile telephones and similar devices.

Technical data

Charging current:	max. 3 A
Rated voltage	
- Primary:	AC 100 – 240 V, 50/60 Hz
- Secondary:	5 V (± 5%)
Standby:	≤ 0.15 W
Installation depth:	32 mm
Ambient temperature:	+10 °C to +40 °C
Efficiency:	≥ 75%
Compliant with standards:	DIN EN 60950-1/A2

Scope of supply

- USB cable type A is not included with delivery.