

**USB power supply insert, 2-gang  
Type A / type C**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
white	2349 00	1/5	66.45	02	4010337104681
black	2369 00	1/5	66.45	02	4010337075905

**Features**

- Charging option for up to two end devices simultaneously using USB cable type A and type C.
- Suitable as a charging device, e.g. for mobile telephones and similar devices.

**Technical data**

Charging current:	max. 3 A
Rated voltage	
- Primary:	AC 100 – 240 V, 50/60 Hz
- Secondary:	5 V (± 5%)
Standby:	≤ 0.15 W
Installation depth:	32 mm
Ambient temperature:	+10 °C to +40 °C
Efficiency:	≥ 75%
Compliant with standards:	DIN EN 60950-1/A2

## Scope of supply

- USB cables are not included with delivery.

---