

**Network connection box insert cat.6A, 2-gang  
Insulation displacement connectors**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	2452 00	1	37.89	01	4010337881797

**Features**

- Shielded network connection box cat.6A with two RJ45 jacks (8/8) for data transfer rates up to 10 Gbit-Ethernet in accordance with IEEE 802.3an.
- 45° angled socket outlet for parapet trunking, floor tank and flush-mounted installation.
- Cable entry possible from all directions in 8 x 45° increments.

**Technical data**

Installation depth: 33 mm

**Notes**

- For screw attachment only.