

## Terminal strip, 6-gang 230 V~

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	2479 00	1	88.66	02	4010337110187

### Features

- Terminal strip for wiring room temperature controllers and thermal servos.

### Technical data

Power consumption:	230 V, 50 VA
Fuse	
- 230 V:	T4AH
Quantity	
- Heating zones:	6
- Room temperature controller:	Max. 6
- Servos:	Max. 12
Switch-on current	
- Per servo:	Max. 500 mA
Rated load	
- All drives:	Max. 24 W
Switching capacity	
- Pump control:	2 A / 200 VA inductive
Connections	
- Pump control:	1
- Heating/cooling switchover:	1
- External timer:	1
- Room temperature controller:	6
- 230 V power supply:	1
Direction of action:	NC
Mode of operation:	Type 1/1.C
Protection class:	II

# GIRA Data sheet

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

Ambient humidity: 80% non-condensing

Ambient temperature: 0 to +50°C

Clampable conductor cross-section: 0.2 bis 1.5 mm<sup>2</sup>

---

## Dimensions in mm

B 326,5

H 90

T 50

---