

**British Standard rocker switch (BS EN 60669-1) 20 AX 250 V~ with rocker and control light  
System 55, Off-switch 2-pole**

| Specification      | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--------------------|-----------|--------------|------------------------|----|---------------|
| cream white glossy | 2834 01   | 10           | 40.68                  | 29 | 4010337078814 |
| pure white glossy  | 2834 03   | 10           | 40.68                  | 29 | 4010337078821 |
| anthracite         | 2834 28   | 10           | 41.12                  | 29 | 4010337078845 |
| colour aluminium   | 2834 26   | 10           | 43.82                  | 29 | 4010337078838 |
| black matt         | 2834 005  | 10           | 43.82                  | 29 | 4010337038573 |
| grey matt          | 2834 015  | 10           | 43.82                  | 29 | 4010337087137 |
| stainless steel    | 2834 600  | 10           | 50.05                  | 29 | 4010337022305 |

## Features

- With screw terminals.

## Technical data

|   |  |
|---|--|
| Installation depth:                                 | 24 mm  |
| Connection cross section<br>- for conductors up to: | 2 x 4 mm <sup>2</sup> or 1 x 6 mm <sup>2</sup> |

---

## Notes

- For screw attachment only.
  - BS EN 60669-1.
-