

## Rocker switch insert 10 AX 250 V~ series switch

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
with mounting claws	3105 00	10/100	14.58	01	4010337038856
without mounting claws	3815 00	10	14.58	01	4010337038863

### Features

- Can also be used with 1-gang rocker.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

### Technical data

Installation depth	
- 3105 00:	32 mm
- 24 mm:	23 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm²
Rated output	
- LEDi/CFLi:	100 W