

## Rocker switch insert 10 AX 250 V~ universal off/2-way switch

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
with mounting claws	3106 00	10/100	9.21	21	4010337038931
without mounting claws	3816 00	10	9.21	21	4010337038948

### Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technical data

#### Installation depth

- 3106 00: 32 mm
- 3816 00: 23 mm

#### Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

#### Rated output

- LEDi/CFLi: 100 W

## Notes

- Can also be connected to be illuminated.
-