

**Rocker indicator switch 10 AX 250 V~
with inscription space and orange LED lighting element 230 V~
Circuit breaker, 2-pole**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
grey	3112 30	10	43.24	14	4010337123873

Features

- With orange LED lighting element.
- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic* or would that then be polycarbonate.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected surface-mounted IP44

Technical data

- Connection cross section
- For rigid and flexible conductors up to: 2.5 mm²
- Rated output
- LEDi/CFLi: 100 W

Notes

- Can also be connected to be illuminated.

Scope of supply

- Inscription label "Heizung Ein/Aus" is enclosed.
 - Cable entry 2-gang (twin entry) is enclosed.
 - Orange LED lighting element 230 V~ 0.5 mA is included with delivery.
-