

**Rocker indicator switch insert**  
**10 AX 250 V~ with orange LED lighting element 230 V~ series switch**

| Specification          | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|------------------------|-----------|--------------|------------------------|----|---------------|
| with mounting claws    | 3115 00   | 10           | 28.79                  | 01 | 4010337064473 |
| without mounting claws | 3825 00   | 1            | 28.79                  | 01 | 4010337038900 |

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.

## Technical data

|  |                     |
|--|---------------------|
| Installation depth                         |                     |
| - 3115 00:                                 | 32 mm               |
| - 3825 00:                                 | 23 mm               |
| Connection cross section                   |                     |
| - For rigid and flexible conductors up to: | 2.5 mm <sup>2</sup> |
| Rated output                               |                     |
| - LEDi/CFLi:                               | 100 W               |

## Scope of supply

- Orange LED lighting element 230 V~ 0.5 mA is included with delivery.

---