

## Insert pushbutton switch 10 AX 250 V~intermediate switch

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
with mounting claws	3127 00	10	22.54	01	4010337039198
without mounting claws	3837 00	1	22.54	01	4010337064404

### Features

- In contrast to rocker switches, the rockers on momentary-action switches always return to their original position after each actuation.
- The resulting standardised rocker position enables a tidy and high-quality appearance of the electrical installation.
- The aesthetics are significantly enhanced, especially with multiple combinations, for example with several switches in one frame.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3,5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

### Technical data

#### Installation depth

- 3127 00: 32 mm
- 3837 00: 23 mm

#### Connection cross section

- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

#### Rated output

- LEDi/CFLi: 100 W

## Notes

- Can also be connected to be illuminated.
-