

Rocker switch and rocker button insert 10 A 250 V~ 2-way switch / 2-way momentary contact

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
with mounting claws	3139 00	10	25.78	01	4010337039136
without mounting claws	3869 00	1	25.78	01	4010337064565

Features

- Rocker switch and button in which the left rocker is laid out as a switch and the right rocker is laid out as a push button.
- For switching and colour control of an LED orientation light.
- For controlling motion detectors manually.
- For activating dimmer auxiliary units.
- For controlling switched lighting.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Technical data

Installation depth:	32 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm ²
Rated output	
- LEDi/CFLi:	100 W