

**Rocker with symbol  
Light**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3285 01	1	5.25	01	4010337039600
pure white glossy	3285 03	10	5.25	01	4010337039617
pure white matt	3285 27	5	5.25	01	4010337039631
anthracite	3285 28	5	5.71	11	4010337039648
colour aluminium	3285 26	1	8.63	11	4010337039624
black matt	3285 005	5	8.63	11	4010337067757
grey matt	3285 015	1	8.63	11	4010337110460
stainless steel	3285 600	1	15.23	11	4010337044994

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
  - Quick mounting (3.5 turns per mounting claw).
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-