

**Rocker with symbol
Door**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3287 01	1	5.25	01	4010337039846
pure white glossy	3287 03	10	5.25	01	4010337039853
pure white matt	3287 27	5	5.25	01	4010337039877
anthracite	3287 28	1	5.71	11	4010337039884
colour aluminium	3287 26	1	8.63	11	4010337039860
black matt	3287 005	1	8.63	11	4010337067931
grey matt	3287 015	1	8.63	11	4010337110484
stainless steel	3287 600	1	15.23	11	4010337045250

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-