

Rocker with control window

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3290 01	1	5.24	01	4010337041610
pure white glossy	3290 03	10/100	5.24	01	4010337041627
pure white matt	3290 27	10	5.24	01	4010337041641
anthracite	3290 28	10	5.71	11	4010337041658
colour aluminium	3290 26	1	8.63	11	4010337041634
black matt	3290 005	10	8.63	11	4010337067047
grey matt	3290 015	10	8.63	11	4010337110491
stainless steel	3290 600	1/5	15.20	11	4010337045403

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-