

**Rocker with control window and symbol
socket outlet**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3291 01	1	6.54	01	4010337067108
pure white glossy	3291 03	10	6.54	01	4010337067115
pure white matt	3291 27	1	6.54	01	4010337067139
anthracite	3291 28	1	7.03	11	4010337067146
colour aluminium	3291 26	1	9.97	11	4010337067122
black matt	3291 005	1	9.97	11	4010337067092

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.

- Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-

Notes

- For switchable socket outlets.
-