

Rocker, 2-gang with arrow symbol

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3294 01	10	9.76	01	4010337041191
pure white glossy	3294 03	10/100	9.76	01	4010337041429
pure white matt	3294 27	10	9.76	01	4010337041443
anthracite	3294 28	10	10.27	11	4010337041450
colour aluminium	3294 26	10	13.23	11	4010337041436
black matt	3294 005	10	13.64	11	4010337065746
grey matt	3294 015	10	13.64	11	4010337110507
stainless steel	3294 600	10	19.76	11	4010337045380

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-