

Rocker

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3296 01	10	3.74	21	4010337039341
pure white glossy	3296 03	10/100	3.74	21	4010337039358
pure white matt	3296 27	10/100	3.74	21	4010337039372
anthracite	3296 28	10/100	4.40	11	4010337039389
colour aluminium	3296 26	10	7.36	11	4010337039365
black matt	3296 005	10	7.36	11	4010337065593
grey matt	3296 015	10	7.36	11	4010337110521
stainless steel	3296 600	10	13.90	11	4010337043867

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
 - Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-