

## Rocker

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
pure white	3296 66	5	10.22	13	4010337039457
anthracite	3296 67	5	13.64	13	4010337039464
colour aluminium	3296 65	1	13.64	13	4010337039440

## Features

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected flush-mounted IP44

## Notes

- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.