

## Rocker, 2-gang with arrow symbols

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3297 01	1	9.76	01	4010337065821
pure white glossy	3297 03	10	9.76	01	4010337065838
pure white matt	3297 27	10	9.76	01	4010337065869
anthracite	3297 28	10	10.27	11	4010337065890
colour aluminium	3297 26	1	13.23	11	4010337065852
black matt	3297 005	10	13.23	11	4010337065814
grey matt	3297 015	1	13.23	11	4010337110538

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-