

Rocker with inscription space

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
pure white glossy	3299 66	1	13.67	13	4010337096771
anthracite	3299 67	1	17.09	13	4010337096788
colour aluminium	3299 65	1	17.09	13	4010337096764

Features

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected flush-mounted IP44

Technical data

Height of the inscription label: 12 mm

Notes

- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.

Scope of supply

- Blank inscription label and inscription labels with the "light", "call button" and "door" symbols are enclosed.
