

## Upright rocker, 2-gang

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
pure white glossy	3495 03	1	7.12	01	4010337065647
pure white matt	3495 27	10	7.12	01	4010337065661
anthracite	3495 28	1	7.64	11	4010337065678
colour aluminium	3495 26	1	10.60	11	4010337065654
black matt	3495 005	1	10.60	11	4010337065630
grey matt	3495 015	1	10.60	11	4010337110606
stainless steel	3495 600	1/5	17.12	11	4010337065685

## Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-