

Rocker, 2-gang with control window

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3631 01	1	9.75	01	4010337041108
pure white glossy	3631 03	10	9.75	01	4010337041115
pure white matt	3631 27	1	9.75	01	4010337041153
anthracite	3631 28	1	10.21	11	4010337041160
colour aluminium	3631 26	1	13.21	11	4010337041146
black matt	3631 005	1	13.21	11	4010337065722
grey matt	3631 015	1	13.21	11	4010337110552

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-