

Rocker with control window and inscription space

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3670 01	1	8.63	01	4010337041740
pure white glossy	3670 03	1	8.63	01	4010337041757
pure white matt	3670 27	1	8.63	01	4010337041771
anthracite	3670 28	1	9.18	11	4010337041788
colour aluminium	3670 26	1	12.11	11	4010337041764
black matt	3670 005	1	12.11	11	4010337067078
grey matt	3670 015	1	12.11	11	4010337110569

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).

- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Scope of supply

- Inscription labels with symbols "Light", "Call button" and "Door" are enclosed.
-