

Rocker with symbol and inscription space Bell

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3673 01	1	8.65	01	4010337039990
pure white glossy	3673 03	10	8.65	01	4010337040040
pure white matt	3673 27	10	8.65	01	4010337040200
anthracite	3673 28	5	9.19	11	4010337040217
colour aluminium	3673 26	1	12.12	11	4010337040057
black matt	3673 005	1	12.12	11	4010337067955
grey matt	3673 015	1	12.12	11	4010337110576

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.

- Quick mounting (3.5 turns per mounting claw).
 - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
 - Voltage check possible from the front.
 - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
 - Rigid and flexible conductors can be used.
 - Easily accessible release lever.
 - Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-

Scope of supply

- Blank inscription label enclosed.
-