

Rocker with symbol and inscription space
Bell

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3673 01	1	8.65	01	4010337039990
pure white glossy	3673 03	10	8.65	01	4010337040040
pure white matt	3673 27	10	8.65	01	4010337040200
anthracite	3673 28	5	9.19	11	4010337040217
colour aluminium	3673 26	1	12.12	11	4010337040057
black matt	3673 005	1	12.12	11	4010337067955
grey matt	3673 015	1	12.12	11	4010337110576

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.

- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.

Scope of supply

- Blank inscription label enclosed.
-