

Rocker with symbol and inscription space
Bell

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|------------------|-----------|--------------|------------------------|----|---------------|
| pure white | 3673 66 | 1 | 15.00 | 13 | 4010337040231 |
| anthracite | 3673 67 | 1 | 18.36 | 13 | 4010337040248 |
| colour aluminium | 3673 65 | 1 | 18.36 | 13 | 4010337040224 |

Features

- Plastic: halogen-free, impact-resistant and shatter-proof thermoplastic" or would that then be polycarbonate.
- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.
- Shatter-proof thermoplastic base.
- LED lighting elements can be inserted from the front as standard.
- By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
- Water-protected flush-mounted IP44

Technical data

Height of the inscription label: 12 mm

Notes

- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.

Scope of supply

- Blank inscription label enclosed.
