

## Rocker with control window and symbol Light

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3674 01	1	6.54	01	4010337041870
pure white glossy	3674 03	10	6.54	01	4010337041887
pure white matt	3674 27	10	6.54	01	4010337041993
anthracite	3674 28	10	7.03	11	4010337042099
colour aluminium	3674 26	1	9.97	11	4010337041894
black matt	3674 005	1	9.97	11	4010337067221
grey matt	3674 015	1	9.97	11	4010337110583

### Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.

- Quick mounting (3.5 turns per mounting claw).
  - Easier claw mounting thanks to robust PZ1/slotted/PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-