

**Rocker with control window and symbol  
Light**

| Specification      | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--------------------|-----------|--------------|------------------------|----|---------------|
| cream white glossy | 3674 01   | 1            | 6.54                   | 01 | 4010337041870 |
| pure white glossy  | 3674 03   | 10           | 6.54                   | 01 | 4010337041887 |
| pure white matt    | 3674 27   | 10           | 6.54                   | 01 | 4010337041993 |
| anthracite         | 3674 28   | 10           | 7.03                   | 11 | 4010337042099 |
| colour aluminium   | 3674 26   | 1            | 9.97                   | 11 | 4010337041894 |
| black matt         | 3674 005  | 1            | 9.97                   | 11 | 4010337067221 |
| grey matt          | 3674 015  | 1            | 9.97                   | 11 | 4010337110583 |

**Features**

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.

- Quick mounting (3.5 turns per mounting claw).
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Voltage check possible from the front.
  - Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
  - Rigid and flexible conductors can be used.
  - Easily accessible release lever.
  - Shatter-proof thermoplastic base.
  - LED lighting elements can be inserted from the front as standard.
  - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-