

Rocker with control window and imprint “Heizung Ein/Aus”

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	3678 01	1	6.54	01	4010337042327
pure white glossy	3678 03	10	6.54	01	4010337042358
pure white matt	3678 27	1	6.54	01	4010337042389
anthracite	3678 28	1	7.03	11	4010337042396
colour aluminium	3678 26	1	9.97	11	4010337042372
black matt	3678 005	1	9.97	11	4010337067061

Features

- Floating switch rocker allows automatic and precise positioning of the rocker in the cover frame.
- Quick mounting (3.5 turns per mounting claw).
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Voltage check possible from the front.
- Uniform stripping length (11 mm) for switches and socket outlets guarantees quicker and more efficient mounting.
- Rigid and flexible conductors can be used.
- Easily accessible release lever.

- Shatter-proof thermoplastic base.
 - LED lighting elements can be inserted from the front as standard.
 - By turning the lighting element 180°, you can switch between control lighting and continuous lighting depending on the switch.
-