

**Danish socket outlet 16 A 250 V~  
107-2-D1, DK 1-1b with increased contact protection (Safety Plus)  
System 55**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
cream white glossy	4422 01	1/5	19.87	01	4010337092308
pure white glossy	4422 03	1/5	19.87	01	4010337092322
pure white matt	4422 27	1/5	19.87	01	4010337092346
anthracite	4422 28	1/5	21.03	11	4010337092353
colour aluminium	4422 26	1/5	25.25	11	4010337092339
black matt	4422 005	1/5	25.25	11	4010337092292
grey matt	4422 015	1/5	25.25	11	4010337092315

## Features

- The support ring is earthed in connection with the mounting claws and claw screws.
  - Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technical data

Installation depth:	31 mm
Connection cross section - for conductors from:	1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup>

---

## Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-