

eNet wireless diagnosis device

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	5304 00	1	71.96	42	4010337774006

Features

- Display of the signal quality of selected eNet devices and status messages using LEDs.
- Display of wireless signals from non-eNet wireless transmitters.
- Switching the repeater function of mains operated actuators, transmitters, and energy sensors on or off.

Technical data

Rated voltage:	DC 3 V
Battery	
- Type:	1 x CR 2450N
- UN no.:	3091
Ambient temperature:	-5 °C to +45 °C
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m

Notes

- Batteries are consumables and must be replaced regularly. Please observe the regulations on the disposal of used batteries.
- Diagnosis is only possible if wireless encryption (AES CCM 128) is inactive. Wireless encryption is activated or deactivated via the eNet server Version 2.0.

Scope of supply

- Batteries are included with delivery.