

Power supply DC 12 V 2 A

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
DRA	5319 00	1	67.47	42	4010337774037

Features

- Power supply DC 12 V for the eNet server, eNet wireless receiver module and external camera.

Technical data

Rated voltage	
- Primary:	AC 100 to 240 V, 50/60 Hz
- Secondary:	DC 12 to 14 V
Rated current	
- Secondary:	2 A
Leakage current:	max. 250 µA
Ambient temperature:	-10 °C to +50 °C

Dimensions

Modular width (MW):	2
---------------------	---