

## System 3000 motion detector top unit 1.10 m Standard TX\_44

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
pure white	5373 66	1	81.77	02	4010337050247
anthracite	5373 67	1	88.07	02	4010337050254
colour aluminium	5373 65	1	88.07	02	4010337050230

### Features

- Automatic switching of lighting, depending on the movement of heat and ambient brightness.
- Operation with System 3000 switching or dimming insert or 3-wire auxiliary insert.
- Expansion of the detection range in combination with the 3-wire auxiliary insert.
- Adjustable brightness threshold.
- Sensitivity adjustable in four steps.
- If a System 3000 auxiliary insert with operating top unit or mechanical button is connected to the main unit, the lighting can be switched on or dimmed for the duration of the delay time.

With System 3000 dimming insert

- Switch on with the last brightness set, or a saved switch-on brightness.
- The switch-on brightness can only be saved permanently via the System 3000 auxiliary insert with operating top unit.

### Technical data

Angle of detection:	180°
Brightness value	
- adjustable:	approx. 5 to 500 lx
- fixed:	Day mode
Sensitivity:	25, 50, 75, 100 %
Protection class	
- System 55, Gira F100:	IP20

Illustrations are similar and may deviate from originals.  
Prices valid for United Kingdom with prices valid 01/20.

- TX_44:	IP44
Delay time:	approx. 2 min fixed
Mounting height up to 1.10 m	
- Range of detection forwards:	Max. 32 m
- Range to each side:	Max. 19 m
Ambient temperature:	-20 °C to +45 °C

---

## Notes

- The detection field has a horizontal alignment and may not find a limit when used outdoors. For this reason, ensure that the installation location is suitable for outdoor use or use the 2.20 m motion detector top unit.

---

## Scope of supply

- Clip-on panel to limit the detection range is included with delivery.
-