

**BNC insert, 2-gang
Crimp connection**

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|-------------------|-----------|--------------|------------------------|----|---------------|
| pure white glossy | 5630 03 | 1/5 | 42.62 | 01 | 4010337460251 |
| black matt | 5630 10 | 1/5 | 42.62 | 01 | 4010337460268 |

Technical data

| | |
|---------------------|-------------|
| Wave impedance: | 50 Ω |
| Installation depth: | 25 mm |

Notes

- Not suitable for mounting frames with hinged covers.
- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40