

**Modular Jack RJ45 cat.6A 10 Gbit Ethernet insert**  
**Insulation displacement connectors**

| Specification     | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|-------------------|-----------|--------------|------------------------|----|---------------|
| pure white glossy | 5696 03   | 1/5          | 25.55                  | 01 | 4010337463368 |
| black matt        | 5696 10   | 1/5          | 25.55                  | 01 | 4010337463375 |

**Technical data**

Installation depth  
- Insulation displacement connectors: 35 mm

**Notes**

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40