

**Modular Jack RJ45 cat.6A 10 Gbit Ethernet insert, 4-gang
Gender changer**

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|-------------------|-----------|--------------|------------------------|----|---------------|
| pure white glossy | 5698 03 | 1/5 | 94.39 | 01 | 4010337463429 |
| black matt | 5698 10 | 1/5 | 94.39 | 01 | 4010337463443 |

Technical data

Installation depth
- Gender changer: mind. 24 mm

Notes

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation:

Kaiser electronic boxes

Flush-mounted installation: Kaiser order no.:1068-02

Cavity mounting: Kaiser order no.:9062-94

Concrete installation: Kaiser order no.:1268-40