

Surge protection module

Specification	Order No.	Packing unit	PS	EAN
	0338 00	1	03	4010337128120

Features

- Overvoltage module class III in accordance with IEC 61643-11(type 3, EN 61643-11) for socket outlets with protective conductor connection.
- Mounting by snapping into place on the support ring of the socket outlet.
- With acoustic signalling to indicate faults.
- Label for indicating the socket outlet.
- Protects additional socket outlets in the circuit at a cable length of up to 5 m away.

Technical data

Nominal voltage U_N :	AC 230 V~ (50 Hz)
Maximum continuous voltage U_C :	AC 255 V~ (50 Hz)
Nominal discharge surge current I_n (8/20):	3 kA
Discharge surge current I_{total} (8/20):	10 kA
U_{OC} :	6 kV
max. back-up fuse:	16 A
U_p :	< 1.5 kV
IEC/CEI 61643-11:	class III
EN 61643-11:	Type 3
Protection class:	IP20
Ambient temperature:	-5 °C to +40 °C