

**Gira energy profile with 4 empty units height 1400 mm  
not equipped**

Specification	Order No.	Packing unit	PS	EAN
anthracite	1354 28	1	17	4010337354284
colour aluminium	1354 26	1	17	4010337354260

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

**Features**

- Freely configurable Gira energy profile with 4 empty units.
- The four empty units can be individually equipped with device inserts from the Gira TX\_44 design line or from System 55 by the customer.

**Technical data**

Protection type (device cover closed):	IP44
Dimensions	
- Base:	W 229 x H 10 x D 155 mm
- Profile:	W 142 x H 1400 x D 75 mm

**Notes**

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Mounting using three heavy-duty wall anchors.

- Any required electrical isolation of mains and low voltage can be implemented with the included accessories.
- 

## Scope of supply

- Gira TX\_44 cover frame, 4-gang included with delivery.
  - The mounting materials are included with delivery.
-