

**SCHUKO socket outlet 16 A 250 V~ with LED orientation light and increased contact protection (Safety Plus)  
System 55**

| Specification               | Order No. | Packing unit | PS | EAN           |
|-----------------------------|-----------|--------------|----|---------------|
| cream white glossy          | 4170 01   | 1/5          | 02 | 4010337094708 |
| pure white glossy           | 4170 03   | 1/5          | 02 | 4010337094722 |
| pure white matt             | 4170 27   | 1/5          | 02 | 4010337094746 |
| anthracite                  | 4170 28   | 1/5          | 02 | 4010337094753 |
| colour aluminium            | 4170 26   | 1/5          | 02 | 4010337094739 |
| black matt                  | 4170 005  | 1/5          | 02 | 4010337094692 |
| grey matt                   | 4170 015  | 1/5          | 02 | 4010337094715 |
| stainless steel (lacquered) | 4170 600  | 1/5          | 02 | 4010337094760 |

## Features

- SCHUKO socket outlet with inserted light strip.
- The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.
- The integrated twilight sensor waits until twilight to automatically switch on the LED light and switches it off again when sufficient daylight is detected.
- The LED light is completely integrated in the cover plate, eliminating the need for separate connection.
- The support ring is earthed in connection with the mounting claws and claw screws.
- Quick mounting (approx. 3.5 turns per mounting claw).
- Expanding claws in the housing.
- Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
- Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
- Low installation depth.
- Large, ergonomically shaped release levers.
- Sturdy earth bar with solid earthing fingers.
- Sturdy and corrosion-resistant steel support ring.
- Shatter-proof thermoplastic base.

---

## Technical data

### Power consumption

- Operation: 0.25 W / 0.35 VA / 1.5 mA
- Standby: 0.175 W / 0.25 VA / 1.0 mA

Light intensity: 0.2 cd

Installation depth: 29 mm

Ambient temperature: 0 °C to +40 °C

Conductors: Rigid and flexible

### Connection cross section

- for conductors from: 1.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>

---

## Notes

- Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-