

## eNet Radio switching actuator or momentary-contact actuator, 1-gang

| Specification | Order No. | Packing unit | PS | EAN           |
|---------------|-----------|--------------|----|---------------|
| DRA           | 5433 00   | 1            | 42 | 4010337774273 |

### Features

- The eNet wireless switching or momentary-contact actuator receives telegrams for switching lighting from the eNet wireless receiver module or eNet server via a data line.
- Operating modes: Switching actuator or momentary-contact actuator.
- Status feedback to eNet radio transmitter.
- Scene operation.
- Operating mode buttons: Relay contact stays closed as long as telegrams are being received (max. 60 seconds).

Can be set with eNet server:

- Flashing function.
- Delay time.
- Switch-on/off delay.
- Switch-off pre-warning.
- Minimum switching repeat time.
- Permanent-on, permanent-off.

### Technical data

|                                     |                    |
|-------------------------------------|--------------------|
| Rated voltage:                      | AC 230 V, 50/60 Hz |
| Standby:                            | max. 0.2 W         |
| Ambient temperature:                | -5 °C to +45 °C    |
| Breaking capacity 230 V AC:         | 16 A/AC1           |
| Connected load                      |                    |
| - Light bulbs:                      | 2300 W             |
| - HV halogen lamps:                 | 2000 W             |
| - Wound electronic transformer:     | 1000 VA            |
| - Tronic transformer:               | 1500 W             |
| - Fluorescent lamps, uncompensated: | 920 VA             |
| - LED lights:                       | typically 500 W    |
| - Compact fluorescent lamp:         | typically 500 W    |
| - Capacitive load:                  | 690 VA (560 µF)    |

Connection cross section: Max. 4 mm<sup>2</sup>

Length of the data line: Max. 3 m

---

## Notes

- An eNet wireless receiver module or an eNet server is required to operate this DIN rail adapter.
  - Radio approval is valid for EU and EFTA countries.
- 

## Dimensions

Modular width (MW): 2

---