

## Analogue actuator, 4-gang for KNX

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
DRA	1022 00	1	378.58	26	4010337010708

### Features

- Analogue actuator, 4-gang DRA with integrated bus coupler converts KNX telegrams (1-byte and 2-byte) into analogue output signals.
- These analogue output signals enable heating, air conditioning and ventilation actuators to adapt their initial parameters based on bus information, and to participate in control processes.
- Voltage outputs with short-circuit protection.
- The initial state is indicated by the status LED.
- The initial parameters can be restrained.
- Switch off outputs not required.
- The four outputs are parameterised to voltage or current signals by the software.

### Technical data

KNX medium:	TP256
Number of outputs:	4
Rated voltage:	AC 24 V
Connections	
- KNX:	Connection and junction terminal
- Power supply:	Screw terminals
- Outputs:	Screw terminals
Current signals at the output	
- 0 to 20 mA:	Load $\leq$ 500 $\Omega$
- 4 to 20 mA:	Load $\leq$ 500 $\Omega$
Voltage signals at the output	
- 0 to 1 V:	Load $\geq$ 1 k $\Omega$
- 0 to 10 V:	Load $\geq$ 1 k $\Omega$
Connection cross section:	Max. 4 mm <sup>2</sup>
Ambient temperature:	-5 °C to +45 °C

## Scope of supply

- Connection and junction terminal for KNX included with delivery.

---

## Dimensions

Modular width (MW): 4

---