

## LED orientation light 230 V~ RGB

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
RGB	1169 00	1	102.73	02	4010337042341

### Features

- LED orientation light for use in the private and commercial sectors.
- The orientation light is used, for example, to illuminate stairs or as an orientation aid in dark rooms.
- RGB-LEDs are used as light sources.
- The light colours white, blue, red, green and orange can be set consecutively, or a continuous colour cycle over the entire range of colours (approx. 5 min.) can be started via a control input.
- As a result, any desired colour can be set by stopping at the corresponding point.
- The brightness of the light can be set individually.
- A film which can be inscribed individually can be laid in the cover plate.
- Pictograms for room and route marking can be inserted.

### Technical data

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	1.8 W/2.0 VA
Light intensity (white):	1.2 cd
Installation depth:	30 mm
Connection cross section - maximum:	1.5 mm <sup>2</sup>
Ambient temperature:	0 °C to +40 °C

### Notes

- Professional inscription by the Gira inscription service [www.marking.gira.com](http://www.marking.gira.com).

## Scope of supply

- A stainless-steel slat (for glare reduction) is included with the LED orientation light.
-