

Surface-mounted gong

| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|-------------------|-----------|--------------|------------------------|----|---------------|
| pure white glossy | 1200 03 | 1 | 72.29 | 18 | 4010337200031 |

Features

- The surface-mounted gong in the Gira door communication system is for additional signalling.
- Fully pre-assembled surface-mounted gong. This facilitates fast and clean installation.
- Integrating the design variants of the various design lines creates a uniform appearance of the door communication system and electrical installation.
- Installation possible with or without frame.
- Easy installation using pull-off screw terminals.
- Easy removal of device during renovation work.
- Mounting holes for installation.
- Signal transmission and power supply of the surface-mounted gong via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Parallel connection of up to three gongs or home stations possible.
- One-man commissioning with simple commissioning procedure.
- Operating buttons with integrated LEDs for status display.
- LED display for an incoming call.
- Ringing tone deactivation is possible.
- Ringing tone differentiation for door call, internal call and floor call.
- Selection of ringtone melody – up to five different ringtone melodies can be selected.

The operating buttons on the gong control the following functions

- Setting the ringing tone melody.
- Switching the ringing tone on and off.
- Adjustment of ring tone volume.

Technical data

Power supply: DC 26 V ± 2 V (by 2-wire bus)

Connections

- 2-wire bus: 2 x screw terminal
- Floor-call button: 2 x screw terminal

Ambient temperature: -5 °C to +50 °C

Notes

- A cover frame is required for mounting on a device box.
- A cover frame, 2-gang without crossbar is required for mounting with a cover frame.

Dimensions in mm

| | | | |
|---------|------|-------|------|
| Device: | B 55 | H 127 | T 20 |
|---------|------|-------|------|
