

DCS push button interface, 2-gang

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	1210 00	1/5	41.33	18	4010337210009

Features

- The DCS button interface, 2-gang is used to implement a zero-voltage button signal on the Gira door communication bus.
- The DCS button interface features two separate inputs for the connection of zero-voltage buttons.
- The inputs can either be used to trigger a switching action (e.g. switching lights) via a switching actuator or flush-mounted switching actuator, or they can be assigned to a home station.
- The DCS button interface is intended for installation in a device box behind a conventional button.

Technical data

Power supply:	DC 26 V \pm 2 V (by 2-wire bus)
Ambient temperature:	-5 °C to +50 °C
Connections	
- 2-wire bus:	2 x plug terminal
Number of inputs:	2

Notes

- The button is connected using a 3-wire, approx. 20 cm long connection cable. This connection cable can be extended to a maximum of 5 m.
- When the button interface is assigned to a home station, the two inputs function differently: Input 1 triggers a floor call. This input is required when only a 2-wire line is available to connect a home station incl. floor-call button (e.g. when retrofitting an existing door station). Input 2 triggers a door call. This input is required if the automatic door opener for the home station is to be triggered using a mechanical button.

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Dimensions in mm

B 43

H 28

T 15
