

Light profile height 769 mm

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
anthracite	1343 28	1	623.13	17	4010337343288
colour aluminium	1343 26	1	673.34	17	4010337343264

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

Features

- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation light.
- A 5-pole screw terminal for rigid and flexible conductors up to 4 mm² is used for connection.

Technical data

Protection class: IP44

Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Single wall plug mounting.
- Suitable for E27 light sources with energy efficiency classes A++ to E.

Scope of supply

- The mounting materials are included with delivery.
 - Light sources are not included with delivery.
-

Dimensions in mm

Base:	B 229	H 10	T 155
Profile:	B 142	H 769	T 75
