

**Gira energy profile with 4 empty units height 1600 mm
not equipped**

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
anthracite	1356 28	1	1,025.81	17	4010337356288
colour aluminium	1356 26	1	1,098.95	17	4010337356264

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

Features

- Freely configurable Gira energy profile with 4 empty units.
- The four empty units can be individually equipped with device inserts from the Gira TX_44 design line or from System 55 by the customer.

Technical data

Protection type (device cover closed):	IP44
Dimensions	
- Base:	W 229 x H 10 x D 155 mm
- Profile:	W 142 x H 1600 x D 75 mm

Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.

- Mounting using three heavy-duty wall anchors.
 - Any required electrical isolation of mains and low voltage can be implemented with the included accessories.
-

Scope of supply

- Gira TX_44 cover frame, 4-gang included with delivery.
 - The mounting materials are included with delivery.
-