

Blind actuator, 4-gang DC 24 V with manual actuation for KNX

Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
DRA	2154 00	1	247.50	26	4010337082248

Blind actuators with integrated bus coupler, manual activation, and status display for each output. For controlling electrically operated blinds, shutters, awnings, ventilation flaps, or similar hangings.

Features

- Curtain position can be directly controlled.
- Slat position can be directly controlled.
- Behaviour after bus voltage failure and recovery can be set.
- Separately parameterizable movement times with movement time extension for moving into the upper end position.
- Central control of all blind outputs possible.
- Feedback on the curtain or slat position.
- Feedback can be delayed until after the recovery of bus voltage.
- Assignments of up to five different safety functions (three wind alarms, one rain alarm, one frost alarm) or optionally with cyclical monitoring.
- Forced setting function can be realised for each blind output.
- Integration in scenes is possible, 8 internal scenes at the most can be parameterised per channel.
- Memory function for light scenes.
- Solar protection function with fixed and variable curtain or slat positions can be activated.
- Extended sun protection with extensive control functions.
- Integration in temperature management of building possible.
- Blocking of individual outputs manually or with bus.
- Active or passive (object can be read out) cyclical feedback functions.
- Building site operation: Outputs can be operated manually without bus voltage with operating voltage only.
- For low voltage DC 12 to 48 V.
- Independent control of the four blind outputs.

Technical data

KNX medium:	TP256
Connections	
- KNX:	Connection and junction terminal
- Load:	Screw terminals
Rated voltage:	DC 12 to 48 V

Switching voltage DC: DC 12 to 48 V

Switching capacity

- DC 12/24 V: 6 A

- DC 48 V: 3 A

Connection cross section: Max. 4 mm²

Notes

- Installation on DIN top-hat rail.

Scope of supply

- Connection and junction terminal for KNX included with delivery.

Dimensions

Modular width (MW): 4
